

GlobTek, Inc.
 www.globtek.com
 186 Veterans Drive,
 Northvale, NJ 07647
 Tel. (201) 784-1000
 Fax (201) 784-0111

Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African

Model No. GT-46180-1605

Part No./Ordering No. WR9QA3200CL4P066NAR6

Rev F

REVISION HISTORY

REV	DESCRIPTION	SUB	DATE	APPROVED
F	Update ferrite core from 12*20*7.3mm to 14.2*28.5*8.2mm	rchiu	06/13/2017	QA
E	Spec. correction, revise output cord to show ferrite location by strain relief	jsund	10/21/2016	QA
D	Update TUV PSE Digi International mark, correct Digi pn on box labels	emcna	08/03/2016	QA
C	Update O/P cord from 1530 mm to 1200 mm	QA	07/26/2016	QA
B	Correct grounding configuration to Class II.	emcna	07/19/2016	QA
A	Initial release.	emcna	06/28/2016	QA

In Addition to GlobTek Inc.'s renewed ISO9001:2008 - Quality Management System Certification, GlobTek Inc. is now certified to:

ISO13485:2003 - Medical Devices Quality Management System Certification
 ISO14001:2004 - Environmental Management System Certification

ISO Certificates are available online at <http://www.globtek.com/iso-certificates/>

Customer Approval of Specification:

Please approve, sign and send back to GlobTek so we can complete order processing.

A delay in receipt of this form will delay delivery schedule.

Company Name:

Customer P/N:

Quote Number:

Date:

Authorized Representative Name:

Authorized Representative Signature:

The acceptance of this specification and use of the product described in this document indicates the acceptance and binding of the customer to Globtek terms and conditions, which supersede all other agreements, terms, and conditions (<http://en.globtek.com/terms-and-conditions/>).

Footnote:

GlobTek Inc. will not be liable for the safety and performance of these power supplies if unauthorized access and repair occurs. End user should consult applicable UL, CSA or EN standards for proper installation instruction.

Limitation of Use:

GlobTek product are not authorized for use as mission critical components in life support hazardous environment, nuclear or aircraft applications without prior written approval from the CEO of GlobTek Inc.

Contents of this document are subject to change without prior notice.

RELEASED

By N.Frost at 10:33 am, Jun 20, 2017

GT-46180-1605, 16W, 5V@3.2A, Wall Plug-in, Regulated Switchmode AC-DC

PROPRIETARY INFORMATION

PROPRIETARY OF GLOBTEK, INC. ANY REPRODUCTION, DISCLOSURE OR USE OF THIS DRAWING, IN WHOLE OR IN PART, IS HEREBY PROHIBITED EXCEPT AS SPECIFIED IN WRITING BY GLOBTEK, INC.

GlobTek, Inc.
 www.globtek.com
 186 Veterans Drive,
 Northvale, NJ 07647
 Tel. (201) 784-1000
 Fax (201) 784-0111

Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African

Model No. GT-46180-1605


Part No./Ordering No. WR9QA3200CL4P066NAR6

Rev F

POWER SUPPLY INFORMATION

TYPE: Wall Plug-in
 TECHNOLOGY: Regulated Switchmode AC-DC
 CASE COLOR: GlobTek Black
 NAMEPLATE RATED INPUT: 100-240V~, 50-60 Hz, 0.6 A
 INPUT CONFIG: Interchangeable Blades
 WATTS: 16.0
 VOLTS OUT: 5
 CURRENT OUT (Amps): 3.2
 BLADE/CORD INCLUDED: Q-NA(R): Q-Series N. American
 BLADE/CORD INSTALLED: Q-NA(R): Q-Series N. American
 GROUNDING CONFIGURATION: Class II / Double Insulated
 EFFICIENCY LEVEL: VI
 OUTPUT CONFIGURATION: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691
 CONNECTOR PIN OUT: Center Positive (+V)
 LABEL SPECS: Standard GT,L-1186
 PACK SPEC: C-240000XX NA Packaging

Notes/Modifications/Customizations (notes in this section supersede the values shown in the standard spec):



GlobTek, Inc.
 www.globtek.com
 186 Veterans Drive,
 Northvale, NJ 07647
 Tel. (201) 784-1000
 Fax (201) 784-0111

Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African


Model No. GT-46180-1605

Part No./Ordering No. WR9QA3200CL4P066NAR6

Rev F

SUPPLEMENTARY LABEL:

Label to be applied to housing and White box



APPLICABLE LABEL INFORMATION (To include layout, lines, barcodes, etc.) :

- 1) Country of origin: CHINA CN
- 2) Text Label Revision: -
- 3) Digi Part Number: PN:(1P) 24000066, (NOTE: Revision not to be incorporated in Barcode)
- 4)



1P24000066

(Data encoded in the Bar Code - no spaces)

Code 39 or 128, 0.22" high

- 5) YYWW (YY = last 2 digits of year, WW = week all font 0.06" x 0.04")

GlobTek, Inc.
 www.globtek.com
 186 Veterans Drive,
 Northvale, NJ 07647
 Tel. (201) 784-1000
 Fax (201) 784-0111

Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African

Model No. GT-46180-1605

Part No./Ordering No. WR9QA3200CL4P066NAR6


Rev F

MASTER PACKAGE LABELING:

- a. Each master package / container shall be marked using a printed paper label stock and wax based ink to facilitate re-cycleability of kraft paper containers.
- b. The content of each container label, at a minimum, shall contain the following information:
 1. Digi Part Number (PN:),
 2. Digi Purchase Order Number (P.O.NO:),
 3. Quantity per container,
 4. Container number and total number of containers,
 5. Country of Origin,
 6. Digi Part Number revision (Rev:),

Note: Items 1, 2 and 3 shall be displayed in human readable and code 3 or 9 or code 128 bar-code.

 7. The bar-code identifiers (1P), (R), (K) and (Q) shall be added as a 'prefix header' to the bar-code.
 8. Character size – human readable shall be 0.25 inches (6.35 mm) in height, bar-codes shall be 0.5 inches (12.7 mm) in height. Dimension tolerances are ± 15%.
 9. Any other information on the label is at the discretion of the vendor.



IMPORTER NAME FOR TUV PSE MUST SHOW DIGI INTERNATIONAL ON LABEL



Digi International 株式会社

DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE.

GlobTek, Inc.
www.globtek.com
186 Veterans Drive,
Northvale, NJ 07647
Tel. (201) 784-1000
Fax (201) 784-0111

Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African

Model No. GT-46180-1605

Part No./Ordering No. WR9QA3200CL4P066NAR6

Rev F

ELECTRICAL SPECIFICATIONS

A) ELECTRICAL SPECIFICATIONS:

01. Input Voltage: Specified 90-264 Vac, Nameplate rated: 100-240Vac
(85-264Vac range @ 85% of rated load)
02. Input Frequency: Specified 47-63 Hz, Nameplate rated 50-60Hz
03. Inrush Current: No damage. On power when switching on/off repeatedly under any condition.
04. Average Efficiency: 85% Min. CEC Compliant
05. Input power(no load): < 0.1W CEC Compliant
07. Output Voltage tolerance: $\pm 5\%$
08. Line regulation: $\pm 1\%$
09. Output Voltage: Tolerance $\pm 5\%$
10. Turn On Delay: 3000 mS MAX at 115 VAC Full Load
11. Hold Up Time: 10 mS Min at 100 VAC Full Load
12. Ripple Voltage: $\pm 1\%$ or 150 mV whichever is greater, measured at 20 MHz bandwidth with 0.1 uf ceramic capacitor in parallel with 10 uf electrolytic capacitor connected at the end of the output connector at nominal line.

B) PROTECTION

01. Over voltage protection: Output shut down and auto restart
02. Short circuit protection: Output shut down and auto restart
03. Over Load Protection: Output shut down and auto restart

C) SAFETY

01. HI-POT : Input to output : 3000VAC or 4242VDC 10mA 1 minute
02. Touch current: <0.25mA
03. ESD: Contact discharges 8kV, Air discharges 15 kV
04. Fast transients/bursts: 4 kV

D) OTHER:

01. MTBF: 200,000 Hours @ 25°C ambient temperature
02. Operating Temperature: 0°C to 40°C ambient temperature
03. Humidity Operating : 20% to 80%. 0% to 90% relative humidity
04. Elevation up to 4000 m
05. Storage Temperature: -10°C to 70°C
Humidity Storage: 10% to 90%
06. RoHS 2: Complies with EU 2011/65/EU and China GB/T26572-2011


E) ENCLOSURE

01. Housing: High impact plastic, 94V0 polycarbonate, non-vented
02. Size: 74.0 x 43.5 x 34.0 +/-1.0 mm
03. Weight : 68.5 g
04. Markings: Label and/or Pad Printed and/or Molded in the case

GlobTek, Inc.
 www.globtek.com
 186 Veterans Drive,
 Northvale, NJ 07647
 Tel. (201) 784-1000
 Fax (201) 784-0111

Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African


Model No. GT-46180-1605	
Part No./Ordering No. WR9QA3200CL4P066NAR6	Rev F



DERATING CURVE

Typical External Power Supply Derating Curve

(For Efficiency Level V and Efficiency Level VI Products)



GlobTek, Inc.
 www.globtek.com
 186 Veterans Drive,
 Northvale, NJ 07647
 Tel. (201) 784-1000
 Fax (201) 784-0111


Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African

Model No. GT-46180-1605

Part No./Ordering No. WR9QA3200CL4P066NAR6

Rev F

INPUT CONFIGURATION



Grounding Configuration:

Blades/Cord Included: Q-NA(R): Q-Series N. American


Blades/Cord Installed: Q-NA(R): Q-Series N. American

Blade Options for Q Series Wall Plug-in Power Supplies

Data Sheet: <http://en.globtek.com/interchangeable-blades.php>

Insertion Instructions: <http://www.globtek.com/pdf/Instructions-Interchangeable-Blades.pdf>

Video: [Q-Blade Style Instruction Video](#)



INPUT CONNECTOR: Q-Socket (below are available blades configurations which are "not included" (unless stated above); can be purchased separately, package with power supply or as a separate "Q-KIT" if specified

01. United States / Canada / Japan NEMA 1-15P configuration: NA 2 blades, Class II; US/CA/JP P/N: Q-NA(R)

02. Australian AS 3112 configuration: SAA 2 blade, Class II; AU P/N: Q-SAA(R)

03. UK BS 1363 configuration: UK 3 blade with dummy Ground, Class II; GB P/N: Q-UK(R)

GlobTek, Inc.
www.globtek.com
186 Veterans Drive,
Northvale, NJ 07647
Tel. (201) 784-1000
Fax (201) 784-0111

Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African

Model No. GT-46180-1605

Part No./Ordering No. WR9QA3200CL4P066NAR6

Rev F

04. European CEE 7/16 configuration: Europlug 2 pins, Class II; EU P/N: Q-EU(R)
05. Korean KS C8305 configuration: 2 pins, Class II; KR P/N: Q-KR(R)
06. Argentina IRAM 2073 configuration: 2 blades; AR P/N: Class II Q-AR(R)
07. China GB 2099 configuration: 2 blades, Class II; CN P/N: Q-CN(R)
08. India IS 1293 6A/SANS 164-3/BS546 configuration: 5A, 3 pins with Dummy Ground, Class II; IN P/N: Q-IN(R)
09. IEC320/C18 Inlet, Class II; P/N: Q-C18(R)
10. Brazilian NBR6147 configuration: 2 pins, Class II; BR P/N: Q-BR(R)
11. S. African SANS 164-1 configuration: 2 pins with Dummy Ground, Class II; SA P/N: Q-SANS164-1-16A(R)
12. Israel / Malaysia / Singapore British Standard BS 546-15A configuration: 2 pins with Dummy Ground, Class II; P/N: Q-BS546-15A(R)

Kits

01. Q-KIT: 1,2,3,4 above
02. Q-KIT-INTL: 2,3,4 above
03. Q-KIT-6: 1,2,3,4,5,6 above
04. Q-KIT-7: 1,2,3,4,5,6,7 above
05. Q-KIT-8: 1,2,3,4,5,6,7,8 above

GlobTek, Inc.
 www.globtek.com
 186 Veterans Drive,
 Northvale, NJ 07647
 Tel. (201) 784-1000
 Fax (201) 784-0111

Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African

Model No. GT-46180-1605

Part No./Ordering No. WR9QA3200CL4P066NAR6


Rev F

OUTPUT CORD AND CONNECTOR: CLP4/C3691

ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW

CABLE TYPE	UL 1185
CABLE LENGTH (mm)	1200
CABLE TOLERANCE (mm)	+150,-0
WIRE GAUGE (AWG)	18
CONDUCTORS	1C + Shield
HANK DIMENSION (mm)	80 ± 10
CABLE / CONNECTOR OVERMOLD COLOR	GlobTek Black
FERRITE TYPE / DIMENSION	Core Size: 14.2*28.5*8.2
FERRITE # OF TURNS (Definition)	2 Pass thru core (1 turns)
FERRITE DIMENSION FROM STRAIN RELIEF	50 ± 10
FERRITE DIMENSION FROM PLUG	N/A
PLUG TYPE	Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal
OVER MOLD ORIENTATION	Straight
CONNECTOR PIN OUT:	Center Positive (+V)

ADDITIONAL REQUIREMENTS



1. CRITICAL FOR LOCKING NUT TO BE FULLY THREADED.
2. THREAD INSPECTION OF LOCKING NUT BEFORE SHIPPING FROM PRODUCTION IS REQUIRED.
3. FERRITE PLACEMENT 50mm FROM STRAIN RELIEF.

ADDITIONAL OUTPUT PLUG OPTIONS ARE AVAILABLE AT <http://www.globtek.com/connectors/>
 STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <http://www.globtek.com/connectors/>

GlobTek, Inc.
 www.globtek.com
 186 Veterans Drive,
 Northvale, NJ 07647
 Tel. (201) 784-1000
 Fax (201) 784-0111

Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African

Model No. GT-46180-1605


Part No./Ordering No. WR9QA3200CL4P066NAR6

Rev F

LABEL:L-1186

LABEL P/N: Standard GT
 MATERIAL: Flat Thermal Transfer, Imprintable, Polyester Label and/or Pad Printed and/or Molded, and/or Laser Engraved in the case
 BACKGROUND COLOR: Black if housing is Black, White or Silver if housing is White or Gray.
 TEXT COLOR: White or Silver if label is Black Background for Black housing. Black if label is White or Silver background and Housing is White or Gray
 LABEL WIDTH (mm): 29.8
 LABEL HEIGHT (mm): 20.8

Below is the minimum information which will appear on the label. NOTE: in the logo area additional/actual positioning of symbols and text is subjected to change as per agency updates/requirements or additional model approvals become available. Regulatory certifications/label markings may be in logo area on the label or molded into the case housing outside the label area. Information will be shown via label and/or pad printed and/or molded and/or laser engraved in the case. * Date code markings at GlobTek option.



or
DATE CODE B *:
 WWYY
 WW = WEEK
 YY = YEAR

XXX = USA or CHINA

A=ITE Power Supply
 B=P/N: (料号) WR9QA3200CL4P066NAR6
 C=Model (型号) GT-46180-1605
 D=Input (输入) 100-240V~, 50-60 Hz, 0.6 A
 E=Output (输出) 5 V 3.2 A ,16.0W

- AGENCY ONLINE DOCUMENTS <http://www.globtek.info/certs/GT-46180-18VV-X.X/>
- CE EC-Declaration for Medical [Contact GlobTek for more information](#)
- CE EC-Declaration for Industrial/Commercial/ITE http://www.globtek.com/pdf/ec_declaration/a00a000000MFCdnEAH
- RoHS/RoHS2 Declaration http://www.globtek.com/pdf/rohs_cert/01ta0000006xGPNAA2
- REACH Declaration http://www.globtek.com/pdf/iso_certificates/REACH.pdf
- Conflict Minerals Declaration <http://www.globtek.com/pdf/conflict-minerals.pdf>

IPXY rating is based on 3rd party testing and customers should check suitability and test system level IPXY rating before ordering.

GlobTek, Inc.
 www.globtek.com
 186 Veterans Drive,
 Northvale, NJ 07647
 Tel. (201) 784-1000
 Fax (201) 784-0111











Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African

Model No. GT-46180-1605

Part No./Ordering No. WR9QA3200CL4P066NAR6

Rev F

Regulatory Certifications/Label Markings

Logo	Description
	Bureau Of Indian Standards for GT-46180-1812
	Taiwan BSMI R32282 12V, 7.5V for GT-46180
No Logo	CB Certificate IEC 60950-1:2005 2nd Edition + A1:2009 +A2:2013 Report to EN 60950-1:2006 +A11:2009 +A1:2010 + A12:2011 +A2:2013 For 5V-24V only
	CCC to GB4943.1-2011 GB9254-2008 GB17625.1-2012, Tropical <2000
	CE Mark: tested to comply with IEC 61000-4-2:2008 ED.2.0 IEC 61000-4-2:2008 ED.2.0 IEC 61000-4-3:2010 ED.3.2 IEC 61000-4-3:2010 ED.3.2 IEC 61000-4-4:2012 ED.3.0 IEC 61; EMI: Complies with CISPR 22:2008, Class B AS/NZS CISPR 22:2009 +A1:2010, Class B IEC 610
	CHINA SJ/T 11364-2014, China RoHS Chart: http://en.globtek.com/globtek-rohs.php
	UL60950-1, cULus to UL 60950-1 E170507
	Double Insulation - Mark is on the label or Molded in the case
	Certification # TC RU AR46.B.69004 Custom Union of Russia, Belarus and Kazakhstan
	Compliance of this power supply with FCC Part 15, Class B has been demonstrated with a standard output load. The FCC law stipulates that system-level testing is required to demonstrate compliance with the FCC emission limits with the actual system load.
CAN ICES-3(B)/NMB-3(B)	Compliance of this PSU with Industry Canada, Class B demonstrated with a standard output load. The ICES law stipulates that system-level testing is required to demonstrate compliance with the ICES-3 emission limits with the actual system load.
	Indoor Use Only - Mark is on the label or Molded in the case
IP40	Ingress Protection: IP40 to IEC60529:2001 Protection against granular foreign bodies (with I/P cord)
	IRAM certificate DC-E-G71-001.11 to IEC 60950 -1:2005+ A1:2009 + A2:2013

PRECAUCION: PARA USO EN EQUIPOS

PROPRIETARY INFORMATION

PROPRIETARY OF GLOBTEK, INC. ANY REPRODUCTION, DISCLOSURE OR USE OF THIS DRAWING, IN WHOLE OR IN PART, IS HEREBY PROHIBITED EXCEPT AS SPECIFIED IN Page 11 of 16

WRITING BY GLOBTEK, INC.

QA /06/20/2017 9:25:53 AM

GlobTek, Inc.
www.globtek.com
186 Veterans Drive,
Northvale, NJ 07647
Tel. (201) 784-1000
Fax (201) 784-0111

Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African

Model No. GT-46180-1605

Part No./Ordering No. WR9QA3200CL4P066NAR6

Rev F

ELECTRONICOS SOLAMENTE



GlobTek, Inc.

JAPAN TUV R-PSE, Cert. No. JD 50316221, to J60950-1(H26) , J55022(H22),[15V or less]. Please reference the following website for guidelines on PSE regulations:

<http://en.globtek.com/importing-ite-and-medical-power-supplies-ac-adaptors-to-japan/>



GlobTek, Inc.

JAPAN TUV R-PSE, Cert. No. JD 50316221, to J60950-1(H26) , J55022(H22),[15V≤30V]. Please reference the following website for guidelines on PSE regulations:

<http://en.globtek.com/importing-ite-and-medical-power-supplies-ac-adaptors-to-japan/>



GlobTek, Inc.

JAPAN TUV R-PSE, Cert. No. JD 50316221, to J60950-1(H26) , J55022(H22),[30V≤60V]. Please reference the following website for guidelines on PSE regulations:

<http://en.globtek.com/importing-ite-and-medical-power-supplies-ac-adaptors-to-japan/>



Korea KET KC Mark GT-46180-1509-1.5 HU10499-16025A (7.5V Only)



Korea KET KC Mark GT-46180-1812 HU10499-16024A (12V Only)

EFFICIENCY LEVEL VI

Efficiency: complies to section 301 of Energy Independence and Security Act (EISA) complies with Energy Star tier 2 (North America), ECP tier 2 (China), MEPS tier 2 (Australia), Code of Conduct (Europe)

LPS

Limited Power Source

No Logo

Malaysia ST Release Letter GT-46180

IEC60950-1:2005 (ED.2) + A1:2009 + A2:2013, No logo



NOM (Mexico) to NOM-001-SCFI-1993 for GT-46180-1812-Q (12 Volts only)



GlobTek, Inc.

JAPAN TUV Rheinland-PSE GlobTek Inc to J60950-1(H26) , J55022(H22),J3000(H25).Please follow the procedure listed in the following link for proper import to Japan: <http://en.globtek.com/importing-to-japan.php>.



RCM certificate SAA-160017-EA; Australia and New Zealand Regulatory Compliance, Mark (<http://rcm.standards.org.au/rcmfaq/rcmfaq.htm>

RoHS 2

RoHS 2: Complies with EU 2011/65/EU and CHINA SJ/T 11363-2006
<http://www.ce-mark.com/Rohs%20final.pdf>



SGS GS to EN 60950-1:2006 + A11+A1+A12+A2 AFPS GS 2014:01 PAK

GlobTek, Inc.
 www.globtek.com
 186 Veterans Drive,
 Northvale, NJ 07647
 Tel. (201) 784-1000
 Fax (201) 784-0111

Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African

Model No. GT-46180-1605

Part No./Ordering No. WR9QA3200CL4P066NAR6

Rev F



Singapore GT-46180-1812 ICE 60950-1:2005 + A1:2009 +A2:2013 151769-12 (12V only)



Singapore GT-46180-1812 ICE 60950-1:2005 + A1:2009 +A2:2013 160085-12 (7.5V only)

No Logo

South Africa approval NRCS




Ukraine UKRSepro (Document: www.globtek.com/html/iso_certificates/GT_Ukraine.pdf)



Japan: Voluntary Control Council for Interference (VCCI)

WEEE: Complies with EU 2012/19/EU (http://ec.europa.eu/environment/waste/weee/index_en.htm)
 Mark is on the label or Molded in the case



Center Positive (+V)

GlobTek, Inc.
 www.globtek.com
 186 Veterans Drive,
 Northvale, NJ 07647
 Tel. (201) 784-1000
 Fax (201) 784-0111

Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African

Model No. GT-46180-1605


Part No./Ordering No. WR9QA3200CL4P066NAR6

Rev F

PACKAGING

Packing Spec P/N: C-240000XX NA Packaging
 Box Qty: 80
 Gift Box Size (mm): 90.5*73*53
 Gift Box Color: White
 Master Carton Size (mm): 388 x 380 x 245
 Master Carton Cubic Volume (m³): 0.04
 Master GW (Kg): 8.4 kg
 BLADES INCLUDED: Q-NA(R): Q-Series N. American
 BLADE/CORD INSTALLED: Q-NA(R): Q-Series N. American

Specific packaging is required, "no exceptions".



GlobTek, Inc.
www.globtek.com
186 Veterans Drive,
Northvale, NJ 07647
Tel. (201) 784-1000
Fax (201) 784-0111

Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African

Model No. GT-46180-1605

Part No./Ordering No. WR9QA3200CL4P066NAR6

Rev F

INSTRUCTION SHEET

Q Blades Instruction Sheet (not required to be packaged with product)

Insertion Instructions: <http://www.globtek.com/pdf/Instructions-Interchangeable-Blades.pdf>

This manual is Provided to customer within the product specification - it is the responsibility of

the OEM/customer to provide the end system user instructions + warnings for the use of this product in the end system. By accepting this specification the customer/OEM Agrees to these terms.

USER MANUAL FOR Q-BLADE SERIES SWITCHING POWER SUPPLIES

Manual del Usuario. Fuentes de Alimentación Series Q-Blade

WARNING! RISK OF FIRE! SHOCK HAZARD!: To prevent electric shock, do not remove the cover. No user-serviceable parts inside. This unit contains hazardous voltages and should only be opened by a trained and qualified technician. Do not use if bent, cracked, modified or compromised. To avoid the possibility of electric shock, disconnect electric power to the product before connecting or disconnecting.

Advertencia! Riesgo de Fuego! Peligro de Choque eléctrico!

No contiene dentro componentes servibles para el usuario. Desconecte el cable de alimentación antes de quitar la cubierta.

INDOOR USE ONLY!

Únicamente para uso en el interior.

POWER SUPPLY BLADE/CORD: AC Mains voltage should be provided to the power supply by a power supply cords approved to

the national standards in which it will be used. Please use the below table as a guideline for Suitable Power cords.

CABLE DE ALIMENTACIÓN: El voltaje de la CA debe proporcionarse a la fuente de alimentación mediante

los cables de alimentación aprobados conforme a las normas nacionales según las cuales será utilizada. Utilice por favor la tabla mencionada aquí abajo como guía para los cables eléctricos adecuados.

1. Class II model NEMA 1-15P AC power plug with 2 prongs, Q-NA(R)
2. Australian AS 3112 configuration: SAA 2 pins Class II, Q-SAA(R)
3. UK BS 1363 configuration: UK 2 pins Class II, Q-UKY(R)
4. European CEE 7/16 configuration: Europlug 2 PINS, Class II, Q-EU(R)
5. Korean KS C8305 configuration: Q-KR(R)
6. Argentina IRAM 2073 configuration: 2 pins, Class II Q-AR(R)
7. China GR 2099 configuration: 2 pins, Class II Q-CN(R)
8. India configuration: 2 pins, Class II, Q-IN(R)
9. IEC320/C18 Inlet

GlobTek, Inc.
www.globtek.com
186 Veterans Drive,
Northvale, NJ 07647
Tel. (201) 784-1000
Fax (201) 784-0111

Drawing Title: GT-46180-1605, ITE Power Supply, Efficiency Level: VI, Case Color/Style: GlobTek Black, Wall Plug-in, Regulated Switchmode AC-DC, Input Rating: 100-240V~, 50-60 Hz, Interchangeable Blades
<http://en.globtek.com/interchangeable-blades.php>, Output Rating: 16W, 5V@3.2A, Output Configuration: 1200 mm, 18/1C + Shield Cond, UL 1185, Female Barrel 5.5 * 2.1 * 13.8 mm w/ 4 mm Thumb Screw or Equal, Ferrite: Core Size: 14.2*28.5*8.2, GlobTek Black, GT Cord # C3691, Pin Out: Center Positive (+V), Blades/Input Cord: Q-Series N. American, Approvals: Malaysia CCC CB CE China RoHS Double Insulation IP40 Level VI LPS PSE RoHS 2 Ukraine VCCI WEEE CE NOM SGS (Brazil) cUL Taiwan BSMI SG (13.2V) IRAM Korea (12V Only) SG (13.2V) India FCC Korea (12V Only) PSE PSE PSE CAN ICES-3 South African


Model No. GT-46180-1605

Part No./Ordering No. WR9QA3200CL4P066NAR6

Rev F

FUSING: Internal fuse for Line is provided in the power supply. A blown internal fuse is an indication of catastrophic failure of circuit component(s). Repair must be performed by GlobTek, Inc. authorized personnel. Fuses must be replaced with same type and ratings per GlobTek internal documentation.

FUSIBLES: La fuente de alimentación provee un fusible interno para la línea. Un fusible interno quemado es un indicador de una falla catastrófica de los componentes del circuito. La reparación debe ser hecha por personal autorizado de GlobTek, Inc. Los fusibles se deben reemplazar por los mismos tipos y rangos que la documentación interna de GlobTek mencione.



This symbol on an instrument indicates that the user should refer to the operating instructions located in the manual.